

General accessories
NSCH 1M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



In the switching facilities and controllers, the N conductor may need to be merged with the PE conductor at a central point. For this reason, busbars are available that allow a wide range of cables to be connected within a confined space (up to 70 wires on one metre of rail). The cables are connected via a compression piece or a clamping yoke. For the first variant there is no need to bend the lugs. A guide lug at the compression piece grips into the busbar and holds tightly to the compression piece. The clamping yokes can be moved on the busbar and adjusted to the whole wiring in the facility. The busbar can be used without holes in various lengths. The rail holding clamp SH is used for fastening. On longer rails, it can also be aligned between clamping yokes.

General ordering data

Order No.	0280200000
Type	NSCH 1M
Version	General accessories, Busbar, Copper, 1000 mm
GTIN (EAN)	4008190012953
Qty.	1 pc(s).

**General accessories
NSCH 1M**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data
Dimensions

Length	1,000 mm	Width	15 mm
Height	2 mm		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Version	15 x 6 mm busbar connection
---------	-----------------------------

Clampable wires (rated connection)

Type of connection	Screw connection
--------------------	------------------

Dimensions

TS 35 offset	39 mm
--------------	-------

Rated data

Rated current	80 A
---------------	------

Material data

Material	Copper	Colour	Silver
----------	--------	--------	--------

System specifications

Product family	General accessories	Type of connection	Screw connection
Mounting rail	TS 35		

Classifications

ETIM 2.0	EC000485	ETIM 3.0	EC000485
UNSPSC	30-21-18-01	eClass 4.1	27-14-06-04
eClass 5.1	27-14-06-04	eClass 6.0	27-14-92-14
eClass 7.0	27-14-92-14		

Approvals

Approvals