

# 868/914MHz YAGI Antenna


9 Element 824-960MHz Directional 12dBi Antenna

## Electrical Specifications

Frequency Range:	824-960MHz
Nominal Impedance:	50 ohm
Gain:	12dBi @ 868MHz
VSWR:	1.5:1
F/B Ratio:	>15dB
Maximum Input Power:	100w
Polarization:	Vertical
Connector:	SMA male

## Mechanical Specifications

Support Boom Material:	Steel Bracket
Element Material:	Aluminium
Number of elements:	9
Antenna dimensions:	730x165x55mm
Antenna weight:	430g



**Order Code: YAGI-868/914A**