

# Multi-Conductor, Shielded, Non-Plenum

## NEC Type FPLR

**Product Construction:**

**Conductor:**

- 22 thru 12 AWG fully annealed solid bare copper per ASTM B-3

**Insulation:**

- Premium-grade, color-coded S-R PVC
- Color code: See chart below

**Shield:**

- Overall Flexfoil® polyester supported aluminum foil
- Stranded tinned copper drain wire

**Jacket:**

- Premium-grade, red PVC
- Temperature range: -20°C to +75°C
- Sequential footage markings to facilitate installation
- Includes ripcord

**Applications:**


- Wiring of fire alarms
- Smoke alarms
- Voice communications
- Burglar alarms
- Fire protective circuits
- Suggested voltage rating: 300 volts

**Compliances:**

- NEC Article 760 Type FPLR (UL: 75°C, 300V)
- California State Fire Marshall Approved
- RoHS Compliant Directive 2002/95/EC
- Designed to meet UL 1666 Flame Test

**Packaging:**

- Please contact Customer Service for packaging and color options



CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INSULATION THICKNESS		NOM. JACKET WALL		NOMINAL O.D.	
				INCHES	mm	INCHES	mm	INCHES	mm

**22 AWG CONDUCTORS**

<b>E2482S</b>	2	22	Solid	0.010	0.25	0.015	0.38	0.126	3.20
<b>E2484S</b>	4	22	Solid	0.010	0.25	0.015	0.38	0.145	3.68

**18 AWG CONDUCTORS**

<b>E2502S</b>	2	18	Solid	0.010	0.25	0.015	0.38	0.158	4.01
<b>E2503S</b>	3	18	Solid	0.010	0.25	0.015	0.38	0.165	4.19
<b>E2504S</b>	4	18	Solid	0.010	0.25	0.015	0.38	0.183	4.65
<b>E2506S</b>	6	18	Solid	0.010	0.25	0.015	0.38	0.216	5.49
<b>E2508S</b>	8	18	Solid	0.010	0.25	0.015	0.38	0.235	5.97

**16 AWG CONDUCTORS**

<b>E2522S</b>	2	16	Solid	0.010	0.25	0.015	0.38	0.180	4.57
<b>E2524S</b>	4	16	Solid	0.010	0.25	0.015	0.38	0.210	5.33

**14 AWG CONDUCTORS**

<b>E2532S</b>	2	14	Solid	0.013	0.33	0.015	0.38	0.218	5.54
<b>E2534S</b>	4	14	Solid	0.013	0.33	0.015	0.38	0.253	6.43

**12 AWG CONDUCTORS**

<b>E2542S</b>	2	12	Solid	0.013	0.33	0.015	0.38	0.252	6.40
<b>E2544S</b>	4	12	Solid	0.013	0.33	0.015	0.38	0.293	7.44

**Color Code Chart**

NO. OF COND.	COLOR
1	Black
2	Red
3	Brown
4	Blue
5	Orange
6	Yellow
7	Violet
8	Gray