

**Schneider Electric Sensor Competency Center**

1875 Founders Drive

Dayton, OH 45420-4017

Toll Free: (800) 435-2121 • Phone: (937) 252-2121 • Fax: (937) 258-5830

E-Mail: hydepark@us.schneider-electric.com • Web site: www.sesensors.com

**Item # 9007MS04S0202, NEMA Square D Limit Switches 9007MS/ML Miniature Potted 39 mm Metal Body**  
**QUOTE****NEMA Square D Limit Switches 9007MS/ML Miniature Potted 39 mm Metal Body**

9007M, silver contacts, rotary, spr. rtn. CW &amp; CCW, 6' bottom cable

**SPECIFICATIONS**

Body Style/Type	NEMA Square D Limit Switches 9007MS/ML Miniature Potted 39 mm Metal Body
Head Type	Metal Rotary, Spring Return, CW and CCW
Lever Arms	Lever Arm (ordered separately)
Body with Contact Type	1 N.O. / 1 N.C. SPDT Snap Action Form C - Silver
Cable /Connector	6 ft
Enclosure Rating	NEMA 1/2/4/6/6P/12/13; IP67
Contact Configuration	1 N.O./1 N.C.
Contact Operation	Snap Action
Form #1	02
Form #1 Description	Yellow #16 AWG SJTO cable
Form #2	02
Form #2 Description	Yellow #16 AWG SJTO cable
Ampere Rating Continuous	10A/5A
Positive Opening	No

Maximum Voltage Rating	240VAC/28VDC
Actuation	CW and CCW
Actuator Action	Momentary
Operating Torque/Force	48 in-Ounces
Approvals	UL # E42259 CCN NKCR - CSA # LR25490 Class 3211-03 - CE
Conforming to Standards	NEMA and UL type 6P
Body Material	Cast Zinc (fully potted)
Head Material	Cast Zinc
Cable Length	6 ft
Connection Type	#16 AWG SJTO Cable - Yellow
RoHS	No
Operating Temperature Range	-20 to +220° F (-28.9 to +104° C)
Shock Resistance	35G
Vibration Resistance	10G (75 to 1200Hz)
Weight	1.2 lb