

**RS PB-DP T SUB-D****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**IP20 T-piece PROFIBUS-DP**

The distributor for PROFIBUS-DP enables the user to connect it conveniently in the electrical cabinet.

It can be mounted on TS32/35 rails and used to connect standardised PROFIBUS-DP lines. Spur lines can be connected next to the connections. The spur lines should be kept as short as possible. Article number 8788580000 allows you to also connect an analysis/programming device via a 9-pole Sub-D socket.

- Functions of the T-piece
- Good shield contact
- Ample space for connecting the bus line
- Mounts on TS32/35 DIN rail

**General ordering data**

Order No.	<a href="#">8788580000</a>
Type	RS PB-DP T SUB-D
Version	
GTIN (EAN)	4032248477418
Qty.	1 pc(s).

**RS PB-DP T SUB-D****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**Technical data****General data**

Cable diameter, max.	8 mm	Cable diameter, min.	4.5 mm
Conductor O.D.	-	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	Protection degree	IP 20
Type of connection	Screw connection		

**Classifications**

ETIM 3.0	EC000830	ETIM 4.0	EC000830
eClass 6.0	27-06-91-90	eClass 7.0	27-06-91-90

**Approvals**

Approvals