


RING OPTION
(FITS OVER ACCESSORY THREAD)



NOTE 1 - ATTACHMENT TYPE
 00 - NO EYELET OR RING
 01-05 - EYELET REF. (SEE TABLE 2)
 09-25 - RING REF. (SEE TABLE 3)
 CF - SUPPLIED WITH CRIMP FERRULE

	EXAMPLE PART NUMBER 100P633-17-1-C-WR4-17
100P663 =	POLAMCO SERIES
F =	INSERT F FOR FLUROSILICONE GASKET (STANDARD GASKET MATERIAL: SILICONE)
17 =	SHELL SIZE (TABLE 1)
1 =	MATERIAL (ALUMINIUM ALLOY)
C =	PLATING: (TABLE 6)
WR =	LANYARD TYPE: (TABLE 4)
4 =	LANYARD LENGTH (IN INCHES) +1,0"/-0" TOLERANCE
17 =	ATTACHMENT REF. (SEE NOTE 1)

SHELL SIZE	A MAX	B MAX
09	21,0	14,4
11	24,0	17,6
13	29,0	21,4
15	32,0	24,6
17	35,0	27,8
19	38,0	30,5
21	41,0	33,7
23	44,0	36,9
25	47,0	40,0

EYELET REF.	F
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

RING REF.	E MAX
09	11.9
11	15.1
13	18,0
15	21.4
17	24.6
19	27.8
21	30.6
23	34.1
25	36.9

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN 83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

DRAWN J.CLARK SALES APPR DESIGN APPR QUAL APPR ISSUE 4 WEIGHT —	DATE 02/12/2010 DCR 4091 GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°	3RD ANGLE PROJECTION NOT TO SCALE THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP ASSY USED ON: MIL-DTL-38999 SERIES I TITLE: PLUG PROTECTION CAP PART NUMBER: 100P663 SERIES	PAGE 1 OF 1 UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES NCAGE CODE U5792 DRAWING NO: P10327
--	---	--	--	---