


BAND REF.

SB - STANDARD BAND  
 MB - MICRO BAND  
 OMIT FOR NO BAND REQUIRED



SHELL SIZE	A THREAD	B MAX	C MAX	D MAX	E MAX	F MAX	MAX ENTRY
09	M12 x 1.0	18,0	13,1	24,7	25,5	30,5	04
11	M15 x 1.0	21,0	13,9	25,9	26,5	32,2	06
13	M18 x 1.0	24,5	14,5	26,3	31,0	33,7	08
15	M22 x 1.0	27,5	15,5	27,2	37,0	35,2	10
17	M25 x 1.0	31,0	16,1	28,0	40,0	36,9	12
19	M28 x 1.0	34,0	16,8	28,3	44,5	38,5	13
21	M31 x 1.0	37,0	17,1	29,1	49,0	40,1	16
23	M34 x 1.0	40,0	17,7	29,5	51,5	41,6	18
25	M37 x 1.0	43,5	18,4	30,4	53,0	43,1	20

ENTRY SIZE	G	H MAX
03	4,77	13,9
04	6,35	13,9
05	7,92	15,5
06	9,52	17,2
07	11,10	18,7
08	12,70	20,3
09	14,27	21,9
10	15,88	23,5
11	17,47	25,1
12	19,05	26,7
13	20,62	28,3
14	22,23	29,9
15	23,82	31,5
16	25,40	33,1
17	27,00	34,7
18	28,60	36,3
19	30,20	37,9
20	31,80	39,5
21	33,38	41,1
22	35,00	42,7
23	36,58	44,3
24	38,10	45,9

**BTSH1-17-08-2-Z-SB-Lxx**

SERIES  
 CONNECTOR INTERFACE  
 ANGLE  
 SHELL SIZE  
 ENTRY SIZE  
 MATERIAL  
 PLATING  
 BAND REF.  
 OPTIONAL LENGTH (STRAIGHT ONLY - OMIT FOR STANDARD LENGTH: 30MM)

BAND-IT ADAPTOR	<b>SERIES BT</b>
	TO FIT MIL-C-38999 SERIES III & IV (MARINE BRONZE)
<small>THIS DRAWING IS THE COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT WRITTEN CONSENT OF THE COMPANY</small>	
 <b>POLAMCO LTD</b>	<small>WESTON LOCK          LOWER BRISTOL ROAD          BATH BA2 1EP</small>