



Europa **Steel** Enclosures



- ✓ Earth Studs Included
- ✓ Top & Bottom Gland Plates
- ✓ Galvanised Back Plate Included
- ✓ Fixing Brackets Available
- ✓ IP65 Enclosure
- ✓ Strong Steel (Powder Epoxy Coated)

STBKEYLOCK Dimensions

L1	L2	L3	B1	H1	φ D
50mm	32.5mm	50mm	20mm	26.7mm	22mm



listed in
LUCKINSlive™

Key operated barrel
lock also available...





✉ For More **Information**
sales@europacomponents.com

www.europacomponents.com

Tel: 01582 692 440 ♦ Fax: 01582 692 450

Europa Steel Enclosures

- ✓ Body and door manufactured in 1.2 to 1.5mm sheet steel
- ✓ Gland plate manufactured in 2.0mm to 2.5mm sheet steel
- ✓ Enclosure coated with standard cycle thermosetting epoxy polyester powder
- ✓ Body and door RAL7035 (textured finish)
- ✓ Mounting plate in galvanized zinc steel sheet
- ✓ IP65 to EN60 529 NEMA4



Part Number	External Dimension			Gland Plate		Mounting Plate	
Measurement	W (mm)	H (mm)	D (mm)	W1 (mm)	D1 (mm)	W3 (mm)	H3 (mm)
STB302515	250	300	150	130	62	195	245
STB303015	300	300	150	180	62	245	245
STB303020	300	300	200	180	62	245	245
STB403020	300	400	200	180	62	245	345
STB404020	400	400	200	216	62	345	345
STB504020	400	500	200	317	120	345	445
STB604020	400	600	200	317	120	345	545
STB604030	400	600	300	317	120	345	545
STB605020	500	600	200	417	120	445	545
STB806020	600	800	200	417	120	540	740
STB806030	600	800	300	417	120	540	740
STB1006020	600	1000	200	417	120	745	945
STB1008020	800	1000	200	417	120	945	945

www.europacomponents.com

Tel: 01582 692 440 ♦ Fax: 01582 692 450