

Datasheet

Item No. 93.016.0053.0

Connector ST16/2 BS WS

Connector ST16, 2 pole, screw connection, 48V/25A, color black



Item No.	93.016.0053.0
EAN	4015573357402
order unit	100 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Rated current	25 A
Rated voltage	48 V
Pull relief	Yes
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	White
Color of housing inclusive strain relief	Black

Connection Data

Connection cross section stranded	2.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	Hermaphroditic
Number of poles	2
Connection type	Screw connection
Degree of protection (IP)	IP20

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	24 mm
Width	8 mm
Height	21 mm

Drawings