



[new products](#)

[corporate news](#)

[software downloads](#)

[how to use search](#)

[reference](#)

[home](#)

products



B/W Waterproof Bullet with Infrared LED Lighting and 3 Ft Cable - white housing (CVC-320WP/W)

Our B/W weatherproof CCTV camera is 100% waterproof with underwater operation capabilities to a 90 feet maximum. It features a 3.6mm fixed focus lens, infrared LEDs, and built-in electronic iris. It is encased in black brass housing and comes with a clip-on sunshield. A mounting bracket, 3 ft. cable and 12V DC power supply are included. Model also available in black with 60ft. cable: CVC-320WP

Technical Specifications

Resolution	420 line
Image Device	1/3" B/W CCD image sensor
Lens	3.6mm, wide angle
Minimum Illumination	.02 lux without IR LEDs, 0 lux when LEDs are on
Electronic Shutter	Auto 1/60-1/100,000 sec.
Video S/N Ratio	Greater than 48dB
Operating Temperature	- 14 degrees F to 120 degrees F
IR LEDs	8@ 850 NM, controlled by CDS Sensor
Power Supply	12V DC power supply included - UL & CSA listed
Power Consumption	200ma
Mounting Bracket	Included
Dimensions	1-1/2" H x 2" D
Weight	7.4 oz.

Downloads

