

Indoor/Outdoor Labels for General, Lean, Facility & Safety ID

For bins, drawers, tools, equipment and components inside of panels.

- **B-422 Polyester Labels** - Permanent adhesive, good for powder-coated/textured surfaces. Best on flat surfaces. Temp. Range: -40°F to 212°F (-40°C to 100°C). UL recognized.
- **B-428 Polyester Labels** - Permanent adhesive, silver finish. Temp. Range: -40°F to 176°F (-40°C to 80°C). UL recognized.
- **B-483 Polyester Labels** - Permanent adhesive for powder-coated/textured surfaces. Best on flat surfaces Temp. Range: -40°F to 248°F (-40°C to 120°C). UL recognized.
- **B-499 Nylon Cloth Labels** - Permanent adhesive. Pliable for rough or smooth surfaces. Temp. Range: -94°F to 194°F (-70°C to 90°C). UL recognized.
- **B-595 Indoor/Outdoor Vinyl Film** - Permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colors. Temp. Range: -40°F to 248°F (-40°C to 120°C). UL recognized.




Figure 29




Figure 33




Figure 46
(Includes black border)

Diagram	Part Number	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
B-422 Polyester Labels							
Fig. 29	X-7-422	B-422	Polyester	BK on WT	0.500 (12.7)	0.500 (12.7)	350
Fig. 29	X-19-422	B-422	Polyester	BK on WT	1.000 (25.4)	1.000 (25.4)	250
Fig. 29	X-132-422	B-422	Polyester	BK on WT	1.500 (38.1)	1.250 (31.8)	250
Fig. 29	X-30-422	B-422	Polyester	BK on WT	1.500 (38.1)	0.750 (19.1)	250
B-428 Polyester Labels							
Fig. 29	X-17-428-SV-BK	B-428	Polyester	BK on SV	1.000 (25.4)	0.500 (12.7)	500
Fig. 46	X-24-428-SVBB-BK	B-428	Polyester	BK on SV	1.130 (28.7)	0.500 (12.7)	500
Fig. 29	X-29-428-SV-BK	B-428	Polyester	BK on SV	1.500 (38.1)	0.500 (12.7)	500
Fig. 29	X-30-428-SV-BK	B-428	Polyester	BK on SV	1.500 (38.1)	0.750 (19.1)	325
Fig. 29	X-20-428-SV-BK	B-428	Polyester	BK on SV	2.000 (50.8)	1.000 (25.4)	100
B-483 Polyester Labels							
Fig. 29	X-17-483	B-483	Polyester	BK on WT	1.000 (25.4)	0.500 (12.7)	500
Fig. 29	X-20-483	B-483	Polyester	BK on WT	2.000 (50.8)	1.000 (25.4)	100
Fig. 29	X-61-483	B-483	Polyester	BK on WT	2.000 (50.8)	0.500 (12.7)	100
B-499 Nylon Cloth Labels Labels							
Fig. 33	XC-375-499	B-499	Nylon Cloth	BK on WT	0.375 (9.5)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 33	XC-500-499	B-499	Nylon Cloth	BK on WT	0.500 (12.7)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-11-499	B-499	Nylon Cloth	BK on WT	0.750 (19.1)	0.500 (12.7)	275
Fig. 33	XC-750-499	B-499	Nylon Cloth	BK on WT	0.750 (19.1)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-84-499	B-499	Nylon Cloth	BK on WT	0.900 (22.9)	0.500 (12.7)	250
Fig. 33	XC-1000-499	B-499	Nylon Cloth	BK on WT	1.000 (25.4)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-130-499	B-499	Nylon Cloth	BK on WT	1.500 (38.1)	0.750 (19.1)	300
Fig. 29	X-162-499	B-499	Nylon Cloth	BK on WT	1.500 (38.1)	0.500 (12.7)	165
B-595 Indoor/Outdoor Vinyl Film							
Fig. 33	XC-500-595-BL-WT	B-595	Vinyl	WT on BL	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-CL-BK	B-595	Vinyl	BK on CL	0.500 (12.7)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-500-595-GN-WT	B-595	Vinyl	WT on GN	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-OR-BK	B-595	Vinyl	BK on OR	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-RD-WT	B-595	Vinyl	WT on RD	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-BK	B-595	Vinyl	BK on WT	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-RD	B-595	Vinyl	RD on WT	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-YL-BK	B-595	Vinyl	BK on YL	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-BL-WT	B-595	Vinyl	WH on BL	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-CL-BK	B-595	Vinyl	BK on CL	0.750 (19.1)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-750-595-GN-WT	B-595	Vinyl	WH on GN	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-OR-BK	B-595	Vinyl	BK on OR	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-RD-WT	B-595	Vinyl	RD on WT	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-BK	B-595	Vinyl	BK on WT	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-RD	B-595	Vinyl	WH on RD	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-YL-BK	B-595	Vinyl	BK on YL	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)

Note: As of March 2011, B-580 material has been replaced by B-595 material. The updated part numbers are shown in table above. For example: part number "XC-750-580-RD-WT" has been replaced with "XC-750-595-RD-WT".

Indoor/Outdoor labels continued on next page.