



462-6680: Ideal where non contact rpm and simplicity of operation is required at economic cost.

Supplied with Reflective Tape, Batteries, instructions, Certificate of Conformity and is carton packed.

462-6692: Specifically designed to suit the regular user needing both contact and non-contact measurements but yet providing practical easy to use features & high specification of rpm & meters/minute measurement.

462-6709: Highly suitable in a wide variety of applications where in depth speed measurement data monitoring is essential, extremely versatile with measurements in minutes or seconds, with rpm and linear parameters, Maximum, Minimum speed capture, and average speed monitoring, most useful in fluctuating speed applications. Ideal for test, development, production monitoring & as a real diagnostic tool.

462-6692 & 462-6709 are supplied with:

Contact Adaptor, Reflective tape, Batteries, Instructions, Certificate of Conformity and custom moulded carrycase.

- 5 Digit vertical display
- 0.01% ± 1 digit Accuracy
- 0.8 sec or time between pulses (whichever is slowest) Timebase
- $\pm 45^\circ$ Optical angle to reflective target
- Minilamp Light Source
- On Target Indicator and Battery Low Indication in display
- Power Source = 4 x AAA batteries

	462-6680 A2101	462-6692 A2102	462-6709 A2103
Speed Range (rpm)	60-19999	3-99999	60-19999 or 0.05-1666 rps
Linear Speed Range		Meters/min	M/min, Yds/min, Ft/min
Resolution	1 rpm	Max 0.01	M/sec, Yds/sec, Ft/sec
Autoranging	Single fixed	Autoranging	0.001 in Autorange
Optical Range	0.5 metres	1 metre	User selectable 1 metre

333738.277270

Description	Mftrs. List No.	Order Code	Price Each
Optical	A2101	462-6680	
Optical/Contact	A2102	462-6692	
Professional Optical/Contact	A2103	462-6709	
5m x 25mm Reflective Tape	RT5	462-6722	