



FLEXI-BNC90-433


- $\frac{1}{4}$ Wavelength Whip Antenna
- Rugged Flexible Plastic Finish.
- Available as BNC, SMA-Plug, M4 Screw Fixing
- Available as Straight or Right Angle
- Omni-Directional Design
- 50ohm Impedance
- Operating Temp -30 to $+60^{\circ}\text{C}$
- Insulation resistance $500\text{M}\Omega$ @ 500Vdc



Applications

- General Low Power Radio
- M2M Applications


Mechanical Dimensions





FLEXI-BNC90-433

Performance / VSWR Plot



R F Solutions Ltd.,
 Unit 21, Cliffe Industrial Estate,
 Lewes, E. Sussex. BN8 6JL. England.

Email : sales@rfsolutions.co.uk <http://www.rfsolutions.co.uk>

Tel: +44 (0)1273 898 000 Fax: +44 (0)1273 480 661

