

Super SabreLite Zone 1



A robust, reliable and submersible torch with fail-safe switching mechanism. This torch will withstand the most rugged of treatment. Used by firefighters and special forces worldwide. Encapsulated lamp module for additional safety in hazardous areas. T4 temperature rating and anti static coating.



- Submersible to 150 metres
- Impact protection battery tray
- Pre-focused Xenon beam
- Powerfull 12,000 candlepower beam
- Uses 3x C-cell batteries (not supplied)
- Ex II 3 G , Ex N II C T4

339180

Description	Order Code	Price Each
Super SabreLite Torch	507-4290 ●	
Spare Lamp module	507-4307 ●	