

5

4

3

2

1

DRAWING NO.
27-8140-CUST

REVISIONS

OFFICAL RELEASE

01

08-25-09

T W B Y T

Betty 2009.09.08 09:28:58 +08'00'

Description: 50 ohm BNC T Adapter
 Part No: 27-8140
 Application: Adapter
 Crimp Tool: N/A
 Impedance: 50 Ohms
 Fequency Range: 0-4 GHz
 Material: Body Brass Nickel Plated
 Contact Brass Gold Plated
 Insulator Derlin
 Crimp Sleeve Brass Nickel Plated
 Coupling Nut Zinc Nickel Plated

RoHS Compliance: Yes
 Technical Detail: Refer to Emerson Document P/N 27-0000




受控 CONTROLLED DOCUMENT

编号 P/N	27-8140-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	--------------	-----------	----	------------------	-----------



11.1
(.437in)



∅ 9.5
(.374in)

36.0 ±0.5
(1.417in ±.020)

DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY TERRY.W		DATE 08-25-09	
DECIMALS	mm	CHECKED BY TERRY.W		DATE 08-25-09	
X	± 0.5	APPROVED BY THOMAS		DATE 08-25-09	
X.X	± 0.3	U/M		mm	
X.XX	± 0.1	∅		E-1	
ANGLES	± 0.5°				

EMERSON
Network Power

Connectivity Solutions

TITLE
50 OHM BNC T ADAPTER

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

SHEET
1 OF 1

DRAWING NO.
27-8140-CUST

SIZE
A

5

4

3

2

1