

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [63811-5500](#)  
**Status:** **Active**  
**Description:** Hand Crimp Tool for 3.56mm Crimp Terminal, Pin

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**


Product Family	Application Tooling
Series	T0102
Comments	Field Repair, See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Product Name	PremiumGrade™
Survey	<a href="http://www.molex.com//review/apptool_survey.html">www.molex.com//review/apptool_survey.html</a>
Tool Type	Handtool

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents

ATS-6381155HM, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN



**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

T0102Series

**Use With**

Loose piece terminals

Application Tooling Description	FAQ Product #
XRC™ Sealed Terminal Pin, 16 to 18 AWG, Terminal Size 16, Insulation Diameter 1.40 to 2.16mm , Nickel	0845240004
XRC™ Sealed Terminal Socket, 16 to 18 AWG, Terminal Size 16, Insulation Diameter 1.40 to 2.16mm , Nickel	0845250009