

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [501912-2790](#)
Status: **Active**
Description: 0.30mm Pitch Easy-On™ FPC Connector, Right Angle, SMT, Bottom Contact Style, 1.80mm Mated Height, 27 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-501912-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-501912-001 \(PDF\)](#)

General

| | |
|----------------|------------------------|
| Product Family | FFC/FPC Connectors |
| Series | 501912 |
| Product Name | Easy-On™ |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 27 |
| Circuits (maximum) | 27 |
| Color - Resin | Black, Natural |
| Contact Position | Bottom |
| Durability (mating cycles max) | 20 |
| Entry Angle | 90° Angle |
| Mated Height | 1.80mm |
| Material - Metal | Copper, Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | High Temperature Thermoplastic |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Retention | None |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 0.30mm |
| Pitch - Termination Interface | 0.30mm |
| Plating min - Mating | 0.102µm |
| Plating min - Termination | 0.051µm |
| Polarized to PCB | No |
| Stackable | No |
| Surface Mount Compatible (SMC) | Yes |
| Temperature Range - Operating | -20°C to +85°C |
| Termination Interface: Style | Surface Mount |
| Wire/Cable Type | FPC only |


Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.2A |
| Voltage - Maximum | 50V AC (RMS)/DC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|---|
| Packaging Specification | SPK-501912-001 |
| Product Specification | PS-501912-001, RPS-501912-002, RPS-501912-003 |
| Sales Drawing | SD-501912-001, SD-501912-002 |



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[501912Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION