

1

2

3

4

5

CHARACTERISTICS:

MATERIAL:

COLOR: BLACK

OPERATING TEMPERATURE: -20°C UP TO 80°C

COMPLIANCE: LEAD FREE AND ROHS


PACKAGING:

10PCS/BAG

WIRE DIMENSION:

AWG: 20

Terminal A





Terminal B

Wire Length 300mm\*

Terminal A	662 001 137 22
Terminal B	662 001 137 22

RoHS Compliant

\* Note: Wire UL 1007

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
F							
E							
D							
C				APPROVAL: RJ	UNIT: MM	DESCRIPTION: WR-MPC3 FEMALE PRE-CRIMPED CONTACT	SIZE <b>A4</b>
B					SCALE:		
A	18-OCT-11	PDF	GG		SHEET: 1/2	WERI PART NO: 662 162 120 030	
REV	DATE	FILE	BY		DRAW: QL		

1

2

3

4

5


A

B

C

D

Note:  
 1.Dimension  
 Carton Size:40\*30\*20(CM)  
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE  
 .X = +/- 0.2  
 .XX = +/- 0.15

APPROVAL: RJ

UNIT: MM  
 SCALE:  
 SHEET: 2/2  
 DRAW: QL

DESCRIPTION: WR-MPC3 FEMALE PRE-CRIMPED CONTACT  
 WERI PART NO: 662 162 120 030

SIZE  
**A4**