


Magnetic Illuminated Pickup Tool

	<p>Bright LED Light through magnet centre giving 360 degree illumination Overall length fully retracted: 190mm / 7 1/2" Overall length fully extended: 810mm / 32" Magnetic Head diameter: 18mm / 0.7" Magnetic will lift: 1.5 kilo / 3.3 lbs Non slip Soft Grip Moulded Handle, suitable for use with oily or wet hands Packaging: Single unit supplied in blister pack complete with batteries</p>
---	--

	<p>Operation: Rotate magnetic head clockwise to switch on illumination, rotate anti-clockwise to turn off.</p> <p>Battery replacement: Rotate magnetic head fully anti-clockwise to for access to batteries. Remove plastic battery holder and remove the 3 batteries. Replace with 3 x SR44/1.5v Alkaline cells Ensure that all cells are inserted with + sign towards the LED lamp contact. Reassemble the magnetic head</p>
---	---

Manufacturers Code	Description
D02267	Magnetic Illuminated Pickup Tool