

T&B® Fittings



T&B Catalog Number: H050-TB
UPC Number: 78621089955
Description: 1/2" Zinc Hub Connector with thermoplastic insulating throat; sealing ring-Nitrile (BUNA "N"). For use with Rigid/IMC Conduit.
Status: Active

Application

- -- Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
 - -- Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.

General

-Trade Size (inches) -- 1/2
 -Material -- Zinc

Dimension Information

-Dimension A (inches) -- 1 7/16
 -Dimension B (inches) -- 1 9/16
 -Dimension C (inches) -- 7/8
 -Dimension D (inches) -- 3/16
 -Dimension E (inches) -- 19/32

Specifications

-3dmodel Available on Website

Packaging

-T&B Inner Pack -- 25
 -Package in Units -- 100
 -T&B Sold in UOM -- Each
 -T&B Weight Per UOM -- 20.5 lbs. per 100

Application Support

-Spacing Chart Available on Website
 -Rigid/IMC Conduit Fittings Overview & Specification Available on Website

Certifications

-RoHS Compliance -- Yes

Certifications



File Nbr:
 E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com