

5362AI

Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory - 5362AI

Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory



FEATURES

- One-piece brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.
- Auto-ground clip assures positive ground.

5362AI

- Corrosion-resistant models have nickel-plated straps and contacts.

Specifications

DIMENSION INFO

Width U S: 1.625"

Depth U S: .900"

Height U S: 3.281"

LISTING AGENCY INFO

cULus

UL 39121406

BUY AMERICAN ACT COMPLIANCE

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant