

8200RED

## Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 15A, 125V, Red - 8200RED



Extra Heavy-Duty Hospital Grade Duplex Receptacle Back & Side Wire 15amp 125volt Red



### FEATURES

- One-piece nickel-plated brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 - #10 AWG stranded or solid copper-clad conductors.

8200RED

- Auto-ground clip assures positive ground.
- Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).

## Specifications

### **DIMENSION INFO**

Width U S: 1.625"

Depth U S: .900"

Height U S: 3.281"

### **LISTING AGENCY INFO**

cULus

UL 39121406

### **BUY AMERICAN ACT COMPLIANCE**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant