



TLS 2200®/TLS PC Link™ Labels - # PTL-8-439

SIZE:	0.500" W x 50' H (12.700 mm W x 15.240 m H)
MATERIAL:	Permanent Vinyl
QTY/UOM:	1/Roll
CATALOG #:	PTL-8-439
PRODUCT #:	18629

OVERVIEW [SPECIFICATIONS](#)

Description for TLS 2200®/TLS PC Link™ Labels

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): General ID, General Identification, Panel Identification, Patch Panel, Voice/Data Identification

Size: 0.500" W x 50' H (12.700 mm W x 15.240 m H)

Printable Area: 0.500" W x 50' H (12.700 mm W x 15.240 m H)

Max Characters Per Line For Font #2: 50

Max Lines of Text For Font #2: 5

Label Type/Style: Label

Color: White

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl

Material Description: Permanent Vinyl

Brady Material #: B-439

General ID Catalog: [pg. 28](#)

Recommended Ribbon Series: R6010

Suggested Ribbon Part#: R6010

Acceptable Ribbon Series: R6210, R4410 (colors)

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Surface: Smooth, Textured/Rough

Special Properties: Various colors available

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 1/Roll