

LASERTAB® Laser Printable Labels - # LAT-46-707-10

SIZE:	0.500" W x 0.500" H (12.700 mm W x 12.700 mm H)
MATERIAL:	Rough Surface Polyester
QTY/UOM:	10,000/Package
CATALOG #:	LAT-46-707-10
PRODUCT #:	67063

\$243.71 MSRP (\$US)



OVERVIEW SPECIFICATIONS

Description for LASERTAB® Laser Printable Labels

Blank, printable polyester labels for Laser Printers. This material is a UL Recognized Component and CSA Accepted material when printed with designated laser printer toners. See UL File MH17154 and CSA Acceptance Record LS41833 for specific details.

Specification Of LASERTAB® Laser Printable Labels

Application(s): 1-6 Outlet Faceplates, General & Industrial Identification, General Identification, Outlet/Jack ID, Panel Identification, Patch Panel - ID Port, Voice/Data Identification

Agency: CSA Approved, UL Recognized

Approval(s)/Compliance:

Size: 0.500" W x 0.500" H (12.700 mm W x 12.700 mm H)

Sheet Size: 8.500" x 11.000" (215.9 mm x 279.4 mm)

Printable Area: 0.500" W x 0.500" H (12.700 mm W x 12.700 mm H)

Label Type/Style: Label

Horizontal Repeat: 0.600" (15.24 mm)

Color: White

Finish: Matte

Qty Per Row: 13

Material Type: Polyester

Material Description: Rough Surface Polyester

Brady Material #: B-707

Left Margin: 0.400" (10.16 mm)

Printer Compatibility: Laser Printers

Qty Per Sheet: 247

Surface: Smooth, Textured/Rough

Top Margin: 0.875" (22.23 mm)

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Package