


TLS 2200®/TLS PC Link™ Flags - # PTLFP-01-425

SIZE: 1.180" W x 0.788" H (30.000 mm W x 20.000 mm H)
MATERIAL: Permanent Polypropylene
QTY/UOM: 250/Roll
CATALOG #: PTLFP-01-425
PRODUCT #: 11196



OVERVIEW **SPECIFICATIONS**

Description for TLS 2200®/TLS PC Link™ Flags

Flags for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers

Specification Of TLS 2200®/TLS PC Link™ Flags

Application(s): Communications Cables, Panel Identification, Voice/Data Identification, Wire & Cable Marking

Agency Approval(s)/Compliance: CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

Size: 1.180" W x 0.788" H (30.000 mm W x 20.000 mm H)

Printable Area: 1.180" W x 0.788" H (30.000 mm W x 20.000 mm H)

Label Type/Style: Label

Color: White

Finish: Matte

Qty Per Row: 1

Material Type: Polypropylene

Material Description: Permanent Polypropylene

Brady Material #: B-425

General ID Catalog: pg. 26

Recommended Ribbon Series: R6210

Suggested Ribbon Part#: R6210

Cable Type: Fiber Strand

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Special Properties: Excellent solvent resistance

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll