



I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels - # WML-317-292

SIZE:	1.500" W x 1.250" H (38.100 mm W x 31.750 mm H)
MATERIAL:	Self-Laminating Vinyl
QTY/UOM:	250/Roll
CATALOG #:	WML-317-292
PRODUCT #:	32420

OVERVIEW **SPECIFICATIONS**

Description for I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Printable, self-laminating vinyl labels for the I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus printers. This material is UL Recognized to UL969 Labeling and Marking Standard when printed with the Brady Series 2000, 5000, and 7300 dot matrix ribbons. See UL files MH10939 for specific details.

Specification Of I.D. PRO® Plus, LS2000 & BradyMarker™ XC Plus Printer Labels

Application(s): Panel Identification, Wire & Cable Marking

Agency: UL Recognized

Approval(s)/Compliance:

Size: 1.500" W x 1.250" H (38.100 mm W x 31.750 mm H)

Printable Area: 1.500" W x 0.500" H (38.100 mm W x 12.700 mm H)

Max Characters Across: LARGE - I.D. PRO: 10, LS2000: 11. SMALL - I.D. PRO: 15, LS2000: 23

Max Lines of Print: I.D. PRO: 3, LS2000: 4

Label Type/Style: Self-Laminating Label

Color: White/Translucent

Finish: Matte

Qty Per Row: 1

Material Type: Vinyl

Material Description: Self-Laminating Vinyl

Brady Material #: B-292

Safety Catalog: pg. 126

Recommended Ribbon Series: R5000

Printer Compatibility: BradyMarker XC Plus, I.D. PRO Plus, LS2000

Special Properties: Self-Extinguishing, Self-Laminating

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll