


M18 FUEL™ 1/4" Hex Impact Driver Kit- CP Batteries 2653-22CT

5.0 [Read 2 Reviews](#) [Write a Review](#)



At only 5-1/2" in length and 3 lbs, the M18 FUEL™ 1/4" Hex Impact Driver delivers maximum performance in a compact size. The 2653 features a POWERSTATE™ Brushless Motor for up to 3X longer motor life and increased power. REDLINK PLUS™ Electronic Intelligence allows the operator to choose between 3 fastening modes with the DRIVE CONTROL™ feature: Mode #1 is for precision work (0-850 RPM, 200 in-lbs of torque,) Mode #2 helps prevent damage to fasteners and material (0-2,100 RPM, 700 in-lbs of torque) and Mode #3 delivers maximum performance for the toughest applications (0-2,900

Includes

- 2653-20 M18 FUEL™ 1/4" Hex Impact Driver
- (2) M18™ REDLITHIUM™ Compact Battery Packs
- 30-Minute Multi-Voltage Charger
- Belt Clip
- Carrying Case

FEATURES

Milwaukee® POWERSTATE™ Brushless Motor runs cooler, lasts longer and delivers up to 55% faster application speed

REDLINK PLUS™ Electronic Intelligence allows the operator to choose between 3 fastening modes with Milwaukee's proprietary DRIVE CONTROL™ feature

The Milwaukee® REDLITHIUM™ Battery Pack is the most durable pack on the market and provides up to 50% more run time

SPECIFICATIONS

| | |
|-------------------------|------------------------------------------------|
| Peak Torque | 1600 in-lbs |
| Max RPM | 0-2,900 |
| Max IPM | 0-3,600 |
| Charger | NEW M18™ and M12™ Multi-Voltage Charger |
| On Board Fuel Gauge | Fuel Gauge on Battery |
| LED Light | Yes |
| Tool Weight (w/battery) | 3.0 lbs |
| Tool Length | 5-1/2" |

RELATED ARTICLES

Milwaukee® Continues to FUEL Innovation with M18 FUEL™ 1/4" Hex Impact Driver

REVIEW SNAPSHOT® by PowerReviews

5.0 (based on 2 reviews)

[WRITE A REVIEW](#)