


Please wait for menu to be constructed

Flexible Cords and Cables

Nylon cord grip connector

Nonmetallic Liquidtight Strain Relief Connector - straight



- Weather Stabilized Nylon
- Temperature Rating: -34 ° C to +105 ° C
- Meets Coast Guard CG293

Dimension Information In F.P.S (U.S)

[Display in metric standards \(C.G.S\)](#)

Catalog No	Cord Range	Dim A (In.)	Dim B (In.)	Dim C (In.)	Hub Size	Throat Dia (In.)
2922NM	.500-.750	1.406	2.156	0.625	1/2?	0.550

Packaging Information

Catalog#	Unit Quantity	Standard Quantity Package	Weight (lbs.)	Weight UOM
2922NM	25	100	6.650	Per 100

Listed / Certified By



UL Listed

(Catalog# 2922NM)
(File# 13938)

[Smart Search Results](#)

[View Product Category](#)

[Print Back](#)