


Please wait for menu to be constructed

Flexible Cords and Cables
 Nylon cord grip connector
 Nonmetallic Liquidtight Strain Relief Connector - straight



- Weather Stabilized Nylon
- Temperature Rating: -34 ° C to +105 ° C
- Meets Coast Guard CG293

Dimension Information In F.P.S (U.S)

[Display in metric standards \(C.G.S\)](#)

Catalog No	Cord Range	Dim A (In.)	Dim B (In.)	Dim C (In.)	Hub Size	Throat Dia (In.)
2932NM	.500-.750	1.406	2.188	0.625	3/4?	0.790

Packaging Information

Catalog#	Unit Quantity	Standard Quantity Package	Weight (lbs.)	Weight UOM
2932NM	10	100	1.600	Per 100

Listed / Certified By



UL Listed

(Catalog# 2932NM)
 (File# 13938)

[Smart Search Results](#) [View Product Category](#)

[Print Back](#)