

**3M™ Chemicals for Electronics Markets****Products**

- Aerosol Cleaners
- + Battery Materials
- Electronic Liquids
- Electronic Coatings
- Electronic Surfactants
- Engineered Fluids
- 1230 Fire Protection Fluid
- Organic Electronics
- Performance Fluids
- Specialty Gases

Solutions

- Aerospace
- Archives & Museums Fire Protection
- Automotive & Transportation
- Data Processing & Control Rooms
- Electronics
- Fire Protection
- Hard Disk Drive
- Marine
- Medical Devices
- Military
- Museum & Preservation
- Oil & Gas
- Precision Optics
- Semiconductor
- Telecommunications

Resources

- Contact Us
- MSDS
- 3M RoHS/REACH Declaration
- Tech Support
- Technical Documents and Literature
- Where to Buy

[Product Catalog for](#) > [Electrical Products](#) > [Wire Fasteners](#) > [Cable Ties](#) > [Cable Ties](#) >

3M™ Plain Cable Tie PB4BK18-M

[Printer-friendly format](#)**The 3M™ Plain Cable Tie PB4BK18-M is 4" in length. Black color. 18 lb tensile strength. 1000 per bag. (Replaces product number: 41930)**

3M Id : 80-6114-6985-1

GTIN(UPC/EAN) : 0 00 51128 59326 4

Characteristics

Agency Approvals	UL
Cable Length	4.1 Inch
Cable Length (mm)	104.14 mm
Color	Black
Country of Origin	USA
EU RoHS Compliant	Yes
Indoor/Outdoor	Indoor
Maximum Bundle Diameter	0.75 Inch
Maximum Bundle Diameter (mm)	19.1 mm
Maximum Operating Temperature	85 Degree Celsius
Maximum Operating Temperature (Celsius)	85 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	185 Degree Fahrenheit
Mil Spec	MS3367-4-0
Minimum Bundle Diameter	0.0625 Inch
Minimum Bundle Diameter (mm)	1.6 mm
Tensile Strength	18 Pound
Tensile Strength (kg)	8.16466 Kilogram
Thickness	0.035 Inch
Thickness (mm)	0.9 mm
Width	0.1 Inch
Width (mm)	2.5

