


# RM-ECs Controller



The RM-ECs controller is for use with the full range of eblm-papst EC fans. Powered by the 10VDC output from the motor, it provides variable speed control with 5 speed settings. Each setting can be adjusted during commissioning between 0 % to 100% speed.

	Supply Voltage	Maximum Ambient Temperature	IP Rating	Height	Width	Depth	
Part Number	VDC	°C		mm	mm	mm	
RM-ECs	10	50	54	94	94	80	
CN1064 (Unboxed)	10	50	00	68	60	73	

- Can control multiple fans running at the same speed
- Step control knob for 5 variable speed setting
- Cable entries 4 x M16 or M20
- 4mm mounting holes
- No separate power supply required



\*Optional