



Emer.stop/swit.off,45mm,key release MS1



Powering Business Worldwide™


Part no.

M22-PVS45P-MS1

Article no.

121468

Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Emergency stop pushbutton/ emergency-stop button
Description			Individual lock mechanism MS1 Not suitable for master key systems
Construction type			Palm-tree shape
Diameter	∅	mm	45
Colour			
Mushroom head			Red
RAL Value			RAL 3000
			
Function			Key operation lock mechanism
Illumination			Without illumination
Front ring			without front ring
Connection to SmartWire-DT			no
Instructions			Release by turning with key
Information about equipment supplied			With one key
Notes			
			Tamper-proof according to ISO 13850, EN 418
			Max. contacts to be fitted together: 4 x M22-(C)K...
			With 1 key
			Release by using the key

Approvals

NA Certification

Request filed for UL and CSA

General

Standards			IEC/EN 60947 VDE 0660
Lifespan, mechanical	Operations	x 10 ⁶	> 0.1
Operating frequency	Operations/ h		≅ 600
Actuating force		n	50
Protection type			IP67, IP69K
Climatic proofing			Damp heat, constant to IEC 60068-2-78 Damp heat, cyclic to IEC 60068-2-30
Ambient temperature		°C	
Open		°C	- 25 - + 70
Mounting position			As required
Mechanical shock resistance		g	50 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27

Technical data ETIM 4.0

With bezel			No
Unlocking method			Key-release
Lens design			Round

Suitable for illumination		No
Hole diameter	mm	22
Suitable for emergency switching off		YES
Color button		red
Width of opening	mm	22
Height meter opening	mm	6
Protection type (IP)		IP67
Material front ring		-
Diameter cap	mm	45
Momentary		No
Switching function latching		YES
Design of button		flush

Dimensions

