



C-Taps		
Burndy Cat. No.	Die Cat. No.	T&B Cat. No.
YGHC2C2	HBKC	CTP22
YGHC26C2	15501A	CTP202
YGHC26C26	15501A	CTP2020
YGHC29C26	15G86R	CTP25020
YGHC29C29	15G86R	CTP250250
YGHC34C26	15G121R	CTP50020
YGHC34C29	15G121R	CTP500250
YGHC34C34	15G121R	CTP500500



Figure 6 to 6 Compression Ground Grid Connectors		
Burndy Cat. No.	Die Cat. No.	T&B Cat. No.
YGL2C2	15501A	54855L
YGL29C2	15G86R, 15501A	54856L
YGLC29C29	15G86R	54875L
YGL34C2	15G126R, 15501A	54885L
YGL34C29	15G126R, 15G86R	54895L
YGL34C34	15G121R	54900L



Figure 6 Compression Ground Tap Connectors		
Burndy Cat. No.	Die Cat. No.	T&B Cat. No.
YGHP29C2	15G86R	54855
YGHP29C26	15G86R	54860
YGHP29C29	15G86R	54865CK
YGHP34C26	15G126R	54890
YGHP34C29	15G126R	54895
YGHP34C34	15G126R	54900



Dual-Rated Splicer/Reducer			
Burndy Cat. No.	Max.	Min.	T&B Cat. No.
AMS2	2	14	ASR0214
AMS0	1/0	14	ASR1114
AMS250	250	6	ASR2506
AMS350	350	6	ASR3506
AMS750	750	250	ASR7525



U-Bolt and Water Pipe Clamps	
Burndy Cat. No.	T&B Cat. No.
GAR1429	6UV7825
GAR3903	3903
GAR3905	3905



Insulation Piercing Connectors			
Burndy Cat. No.	Main	TAP	T&B Cat. No.
BIPC1/0-2	1/0-8	2-8	IPC1102
BIPC4/0-6	4/0-1/0	1/0-6	IPC4111
BIPC4/0-1/0	4/0-1/0	4/0-1/0	IPC4141
-	500-350	4/0-4	IPC5041
BIPC350-350	350-4/0	350-4/0	IPC3535
BIPC500-4/0	350-4/0	4/0-10	IPC3541



Copper Split Bolts				
Burndy Cat. No.	Equal Main & Tap	Min. Tap w/ 1 Main Max.	Inner Pack Qty	T&B Cat. No.
KS90	10-12	14 SOL.	100	9H
KS15	8-10	14 SOL.	100	8H
KS17	6-8	14 SOL.	100	6H
KS20	4-8	14 SOL.	100	4H
KS22	2-6	14 SOL.	100	2H
KS25	1/0-4	14 SOL.	50	10H
KS26	2/0-2	14 SOL.	25	20H
KS27	4/0-2	6 SOL.	25	30H
KS29	250-1	8	25	40H
KS31	350-250	1/0 STR.	1	350M
KS34	500-400	2/0 STR.	1	500M
KS39	1000-800	4/0 STR.	1	750M



Dual-Rated Split Bolts			
Burndy Cat. No.	Inner Pack Qty	Std. Pack Qty	T&B Cat. No.
KSU17	100	600	6HPS
KSU20	100	400	4HPS
KSU22	100	400	2HPS
KSU23	25	100	1HPS
KSU25	50	200	10HPS
KSA1/0	25	250	APS11

Atlantic Region

Thomas & Betts Limited
106 Chain Lake Drive, Unit 2C
Halifax, Nova Scotia B3S 1A8
Tel.: (902) 450-1307
Toll Free: 1-877-862-4357
Fax: (902) 450-1309

Quebec Region

Thomas & Betts Limited
7900 Taschereau Boulevard
Building D, Suite 108
Brossard, Quebec J4X 1C2
Tel.: (450) 466-1102
Toll Free: 1-800-465-1399
Fax: (450) 466-1163

Ontario Region

Thomas & Betts Limited
2000 Argenta Road
Plaza 5, Suite 500
Mississauga, Ontario L5N 2R7
Tel.: (905) 858-1010
Toll Free: 1-877-291-7771
Fax: (905) 858-1080

Western Region

Thomas & Betts Limited
6531-148th Street, #1
Surrey, British Columbia
V3S 3C5
Tel.: (604) 598-9811
Toll Free: 1-866-540-8220
Fax: (604) 598-9840

Thomas & Betts Limited
4836 Eleniak Road
Edmonton, Alberta T6B 2S1
Tel.: (780) 424-7092
Toll Free: 1-888-664-5666
Fax: (780) 424-7093
Toll Free: 1-866-424-4082

CONNECTORS



Color-Keyed®
Blackburn®

Burndy to T&B Cross-Reference

One-Hole Standard-Barrel Lugs

Burndy Cat. No.	Description	T&B Cat. No.
YA8CLBOX	8 AWG COP 1H LUG	54104
YA8CL1BOX	8 AWG COP 1H LUG	54130
YA8CL2BOX	8 AWG COP 1H LUG	54131
YA8CL3BOX	8 AWG COP 1H LUG	54132
YA6CLBOX	6 AWG COP 1H LUG	54105
YA6CL1BOX	6 AWG COP 1H LUG	54134
YA6CL3BOX	6 AWG COP 1H LUG	54135
YA6CL4BOX	6 AWG COP 1H LUG	54136
YA4CL1BOX	4 AWG COP 1H LUG	54138
YA4CL3BOX	4 AWG COP 1H LUG	54139
YA4CL4BOX	4 AWG COP 1H LUG	54140
YA3CL	3 AWG COP 1H LUG	54142-TB
YA2CLBOX	2 AWG COP 1H LUG	54142-TB
YA2CL2BOX	2 AWG COP 1H LUG	54107
YA2CL4BOX	2 AWG COP 1H LUG	54143TB
YA1CLBOX	1 AWG COP 1H LUG	54147
YA1CL4BOX	1 AWG COP 1H LUG	54148
YA1CL6BOX	1 AWG COP 1H LUG	54150
YA25LBOX	1/0 AWG COP 1H LUG	54153TB
YA25L4BOX	1/0 AWG COP 1H LUG	54109
YA25L6BOX	1/0 AWG COP 1H LUG	54155TB
YA26LBOX	2/0 AWG COP 1H LUG	54110
YA26L6BOX	2/0 AWG COP 1H LUG	54160
YA27L4BOX	3/0 AWG COP 1H LUG	54111
YA27LBOX	3/0 AWG COP 1H LUG	54165-TB
YA28LBOX	4/0 AWG COP 1H LUG	54170
YA28L4BOX	4/0 AWG COP 1H LUG	54112
YA29LBOX	250 KCMIL COP 1H LUG	54113
YA31LTC38FX	HYLUG 1H LUG	256-30695-112

Two-Hole Long-Barrel Lugs

Burndy Cat. No.	Description	T&B Cat. No.
YA6C2N	6 AWG COP 2H LUG	54105
YA4C2N	4 AWG COP 2H LUG	256-30695-733
YA2C2N	2 AWG COP 2H LUG	54811BE
YA1C2N	1 AWG COP 2H LUG	54857BE
YA252N	1/0 AWG COP 2H LUG	256-30695-593
YA262N	2/0 AWG COP 2H LUG	54862BE
YA272N	3/0 AWG COP 2H LUG	54864BE
YA282N	4/0 AWG COP 2H LUG	54866BE
YA292N	250 KCMIL COP 2H LUG	54868BE
YA302N	300 KCMIL COP 2H LUG	54870BE
YA312N	350 KCMIL COP 2H LUG	54872BE
YA342N	500 KCMIL COP 2H LUG	54876BE
YA362N	600 KCMIL COP 2H LUG	54878BE
YA392N	750 KCMIL COP 2H LUG	54880BE

Standard-Barrel Splices

Burndy Cat. No.	Description	T&B Cat. No.
YS8CLBOX	8 AWG COP BUTT SPLICE	54504
YS6CLBOX	6 AWG COP BUTT SPLICE	54505
YS4CLBOX	4 AWG COP BUTT SPLICE	54506
YS2CLBOX	2 AWG COP BUTT SPLICE	54507
YS1CLBOX	1 AWG COP BUTT SPLICE	54508
YS25LBOX	1/0 AWG COP BUTT SPLICE	54509
YS27	3/0 AWG COP BUTT SPLICE	54511
YS29LBOX	250 KCMIL BUTT SPLICE	54513

Long-Barrel Splices

Burndy Cat. No.	Description	T&B Cat. No.
YS8C	8 AWG COP BUTT SPLICE	54804
YS6C	6 AWG COP BUTT SPLICE	54805
YS4C	4 AWG COP BUTT SPLICE	54506
YS2C	2 AWG COP BUTT SPLICE	54807
YS3C	3 AWG COP BUTT SPLICE	54807
YS1C	1 AWG COP BUTT SPLICE	54808
YS25	1/0 AWG COP BUTT SPLICE	54509
YS26	2/0 AWG COP BUTT SPLICE	54810
YS28	4/0 AWG COP BUTT SPLICE	54812
YS29	250 KCMIL BUTT SPLICE	54813
YS31	350 KCMIL BUTT SPLICE	54815
YS34	500 KCMIL BUTT SPLICE	54816
YS36	600 KCMIL BUTT SPLICE	54820

Aluminum Splices

Burndy Cat. No.	Description	T&B Cat. No.
YS4CA1	4 AWG ALCU BUTT SPLICE	60512
YS2CA1	2 AWG ALCU BUTT SPLICE	60516
YS26A1	2/0 ALCU BUTT SPLICE	60536
YS28A1	4/0 ALCU BUTT SPLICE	60548
YS31A1	350 KCMIL ALCU BUTT SPLICE	60565

One-Hole Long-Barrel Lugs

Burndy Cat. No.	Description	T&B Cat. No.
YA6C	6 AWG COP 1H LUG	54905BE
YA4C	4 AWG COP 1H LUG	54906BE
YA3C	3 AWG COP 1H LUG	54942BE
YA2C	2 AWG COP 1H LUG	54942BE
YA1C	1 AWG COP 1H LUG	54947BE
YA25	1/0 AWG COP 1H LUG	54949BE
YA26	2/0 AWG COP 1H LUG	54910BE
YA27	3/0 AWG COP 1H LUG	54965BE
YA28	4/0 AWG COP 1H LUG	54970BE
YA29	250 KCMIL COP 1H LUG	54913BE
YA31	350 KCMIL COP 1H LUG	54915BE
YA34	500 KCMIL COP 1H LUG	54919BE

Dual-Rated Mechanical Connectors—1 Conductor

Burndy Cat. No.	Description	T&B Cat. No.
KA6U	6 STR.-14 AWG, 1H	ADR6
KA2U	2 STR.-14 AWG, 1H	ADR2
KA25U	1/0 STR.-14 AWG, 1H	ADR11
KA26U	2/0 STR.-14 AWG, 1H	ADR21
KA29U	250 KCMIL-6 STR., 1H	ADR25
KA31U	350 KCMIL-6 STR., 1H	ADR35
KA34U	500 KCMIL-4 STR., 1H	ADR50

Dual-Rated Mechanical Connectors—2 Conductors

Burndy Cat. No.	Description	T&B Cat. No.
K2A25U	1/0 STR.-14 AWG, 1H	ADR11-21
K2A26U	2/0 STR.-14 AWG, 1H	ADR21-21
K2A29U	250 KCMIL-6 STR., 1H	ADR25-21
K2A31U	350 KCMIL-6 STR., 1H	ADR35-21
KA40U	800 KCMIL-300 KCMIL, 1H	ADR80-21

Dual-Rated Mechanical Connectors—3 Conductors

Burndy Cat. No.	Description	T&B Cat. No.
K3A2U-2	2 STR.-14 AWG, 2H	ADR02-32
K3A36U-2N	600 KCMIL-2 STR., 2H	ADR60-32D

AMT Connectors

Burndy Cat. No.	Description	T&B Cat. No.
2 Port Same Side		
BIT4	4-14 STR.	AMTC4
BIT2/0	2/0-14 STR.	AMT20
BIT250	250 KCMIL-10 STR.	AMT250
2 Port Offset Splice		
BITO4	4-14 STR.	AMTTC4
BITO2/0	2/0-14 STR.	AMTT20
Multiport Same Side		
BIBS4-4	4 PORT 4-14 STR.	AMTS4144
BIBS2/0-3	3 PORT 3/0-6 STR.	AMTS3063
BIBS250-3	3 PORT 250 KCMIL-6 STR.	AMTS25063
BIBS-350-4	4 PORT 350 KCMIL-6 STR.	AMTS35064
BIBS600-4	4 PORT 750-250 KCMIL	AMTS7502504
Multiport Both Sides		
BIBD4-2	2 PORT 4-14 STR.	AMTD4142
BIBD2/0-3	3 PORT 3/0-6 STR.	AMTD3063
BIBD2/0-4	4 PORT 3/0-6 STR.	AMTD3064
Aluminum Splice		
BISR1/0	1/0-14 STR.	AMTSR10
BISR250	250 KCMIL-6 STR.	AMTSR250
BISR500	500 KCMIL-4 STR.	AMTSR500

Ground Clamps

Burndy Cat. No.	Description	T&B Cat. No.
C11K16D	BRONZE, 1/2"-1" PIPE	JDL1
GC15A	ALUM., 1/2"-1" PIPE	AJ
GC18A	ALUM., 1-1/2"-2" PIPE	AJ2

Ground Clamps

Burndy Cat. No.	Description	T&B Cat. No.
GRC12	FOR 1/2" ROD	G4
GRC58	FOR 5/8" ROD	G5
GRC34	FOR 3/4" ROD	G6

H Taps

Burndy Cat. No.	Main	TAP	T&B Cat. No.
YH01	2-6	2-6	WR159
YH02	2-1/0	6-2	WR189
YH03	1/0-2/0	6-2	WR289
YH04	1-2/0	1-2/0	WR279
YH05	3/0-4/0	6-2	WR379
YH06	3/0-4/0	1-2/0	WR399
YH07	3/0-4/0	3/0-4/0	WR419

Copper Mechanical Connectors

Burndy Cat. No.	Description	T&B Cat. No.
KA8C	1 COND. 8 STR.-14 SOL., 1H	L35
KA4C	1 COND. 4 STR.-14 SOL., 1H	L70
KA25	1 COND. 1/0 STR.-8 SOL., 1H	L125BB
KA28	1 COND. 250 KCMIL-6 STR., 1H	L250
KA34	1 COND. 500 KCMIL-4/0 STR., 1H	L400BB

Lay-In Lugs

Burndy Cat. No.	Description	T&B Cat. No.
BGBL250	250 KCMIL-6 AWG	LL2506
BGBL-4	4-14 AWG	LL414

