

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [02-09-1118](#)  
**Status:** **Active**  
**Overview:** Standard .093"  
**Description:** 2.36mm Diameter Standard .093" Crimp Terminal, Dimpled Female, 18-22 AWG, Bag  
**Replacement Part Number:** 2091119

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-43660-9999 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">1381</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .093"</a>
Product Name	Standard .093"
Replacement Part Number	<a href="#">2091119</a>

**Physical**


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm <sup>2</sup>	N/A

**Material Info**

Old Part Number 1381-(P901)L

**Reference - Drawing Numbers**


Product Specification	PS-43660-9999
Sales Drawing	SD-1381-**



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[1381Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638191200</a>
Extractor Tool for .093 and HCS-125 Product Series	<a href="#">0638240200</a>
Extraction Tool	<a href="#">0011030006</a>