

Counterbalance – optimized and more compact mechanism to reduce vibrations

Powerful motor and constant electronics constant cutting speed in the hardest woods, metals and composites

Speed pre-select optimized stroke rate in any material

LED light – for optimal vision while making intricate cuts

4 m H05 power cord maximum freedom of movement while cutting



Sawblade SDS – extra rigidity helps prevent surface breakout when cutting

Swivel vacuum tube prevents snagging on workpiece edges

Precision control – double roller prevents blade wander and deflection

SDS footplate – convenient toolless bevel and fine adjust screw to ensure perfect tool/footplate perpendicularity

Blower function keeps line of cut dust free. On/off function for work w/ cutting oil

Magnesium footplate with plastic insert Reduced workpiece friction eases tool handling while cutting

Counterbalance – optimized and more compact mechanism to reduce vibrations

Powerful motor and constant electronics constant cutting speed in the hardest woods, metals and composites

4 m H05 power cord with ball joint for extra maneuverability and durability

LED light – for optimal vision while making intricate cuts

Speed pre-select optimized stroke rates for any material

Sawblade SDS – extra rigidity helps prevent surface breakout when cutting

Swivel vacuum tube prevents snagging on workpiece edges

Precision control – double roller prevents blade wander and deflection

SDS footplate – convenient toolless bevel and fine adjust screw to ensure perfect tool/footplate perpendicularity

Blower function keeps line of cut dust free. On/off function for work w/ cutting oil

Magnesium footplate with plastic insert Reduced workpiece friction eases tool handling while cutting



GST 140 CE / BCE Professional

The gold standard in precision !

- ▶ **Market leading precision:** Bosch precision control coupled with a new developed sawblade SDS minimize blade wander and blade deflection while cutting
- ▶ **Clear line of sight:** LED lighting system and powerful blower guarantees a clear view to the point of cut
- ▶ **Excellent control:** compact size coupled with minimal vibration ensure absolute control of the tool during cutting
- ▶ **Powerful high performance:** 720 watt motor and electronic feedback control ensure constant cutting speed even in the hardest woods or composite materials



Technical Data	
Power	720 W
Weight kg	2,2 barrel / 2,3 top handle
Stroke Rate	500 - 3100
Saw Blade Change	Keyless: 2 hand SDS
Stroke Length	26 mm
On/off Blower Function	Yes
Footplate Material	Magnesium w friction reducing plastic inlay