



# PRODUCT SPECIFICATION

<b>Brand</b>	Kasp
<b>Product Range</b>	Disc lock hasp and staples
<b>Catalogue number</b>	260
<b>Date</b>	25/03/2010

<p><b>Range Description</b> Disc lock hasp &amp; staples</p> <p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Hardened staple – Extra protection from attack</li> <li>• Zinc plated finish – extra resistance to corrosion</li> <li>• Concealed hinge pins – prevents knock through attack</li> <li>• Concealed fixings – added security</li> <li>• Fixing screws included</li> </ul> <p>When used with a disc type padlock the shackle of the padlock is protected from cropping or sawing attack</p> <p>These Hasp and staples are supplied display packed in sealed blisters or boxed</p>	 <p><b>120mm</b></p>  <p><b>190mm</b></p>
---	---

Item Number	Item Description	EAN No	Commodity code	Carton Qty
K260120D	Disc lock hasp & staple 120mm – display packed	5013969901252	83024100	3
K260190	Disc lock hasp & staple 190mm – boxed	5013969902679	83024100	6
K260190D	Disc lock hasp & staple – display packed	5013969901269	83024100	3

<p>Technical product information</p>	<p><b>Materials</b> – steel with zinc plating – staple is case hardened</p> <p><b>Security rating:</b></p> <table border="1" data-bbox="492 331 878 506"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K260120D</td> <td>9</td> </tr> <tr> <td>K260190</td> <td>9</td> </tr> <tr> <td>K260190D</td> <td>11</td> </tr> </tbody> </table> <p><b>Staple Hole Dia:</b></p> <table border="1" data-bbox="492 617 878 791"> <thead> <tr> <th>Item</th> <th>Staple Hole Dia</th> </tr> </thead> <tbody> <tr> <td>K260120D</td> <td>13</td> </tr> <tr> <td>K260190</td> <td>13</td> </tr> <tr> <td>K260190D</td> <td>13</td> </tr> </tbody> </table> <p><b>Use environment-</b> Normal outdoor use</p> <p><b>Recommended applications-</b> Gates, sheds, garages, shutters and general commercial applications.</p>	Item	Security rating	K260120D	9	K260190	9	K260190D	11	Item	Staple Hole Dia	K260120D	13	K260190	13	K260190D	13
Item	Security rating																
K260120D	9																
K260190	9																
K260190D	11																
Item	Staple Hole Dia																
K260120D	13																
K260190	13																
K260190D	13																
<p>Standards compliance</p>	<p>None applicable</p>																
<p>User health and safety information</p>	<p>None applicable</p>																
<p>RoHS/WEEE compliance</p>	<p>These products do not fall within the scope of RoHS or WEEE regulations</p>																
<p>Material safety data</p>	<p>None applicable</p>																
<p>Warranty</p>	<p>KASP Hasp &amp; staples are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered</p>																
<p>Country of origin</p>	<p>China</p>																

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K260120D	56	120	30	306	115	44	215	336
K260190	55	190	30	445	60	130	47	459
K260190D	55	190	30	445	120	45	310	478

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K260120D	120	220	100	1074		
K260190	135	190	105	2912		
K260190D	130	320	100	1517		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K260120D	24	Blister	7	Backing card			66	Box
K260190	1	Bag	14	Box			158	Box
K260190D	23	Blister	10	Backing card			83	Box