


# PRODUCT SPECIFICATION

<b>Brand</b>	Kasp
<b>Product Range</b>	Europrofile Cylinders
<b>Catalogue number</b>	SDB & SDN
<b>Date</b>	21/10/2011

<p><b>Range Description</b> Kasp Easifit Europrofile Cylinders</p> <p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Kasp Easifit double euro profile cylinders suitable for replacing cylinders in UPVC doors and other applications requiring Europrofile cylinders</li> <li>• Anti-drill for added security</li> <li>• Key both sides for added convenience</li> <li>• 5 Pin cylinder for additional security</li> <li>• 3 keys and replacement screw provided for convenience</li> <li>• Polished brass and Nickel plated finish options</li> </ul>	
---	--

Item Number	Item Description	EAN No	Commodity code	Carton Qty
SDB3030D	Easifit Cylinder Brass 30/30	5013969904000	83014011	6
SDB3040D	Easifit Cylinder Brass 30/40	5013969904017	83014011	6
SDB3535D	Easifit Cylinder Brass 35/35	5013969904024	83014011	6
SDB3545D	Easifit Cylinder Brass 35/45	5013969904031	83014011	6
SDB4040D	Easifit Cylinder Brass 40/40	5013969904048	83014011	6
SDB4050D	Easifit Cylinder Brass 40/50	5013969904055	83014011	6
SDB4545D	Easifit Cylinder Brass 45/45	5013969904062	83014011	6
SDB4555D	Easifit Cylinder Brass 45/55	5013969904079	83014011	6
SDN3030D	Easifit Cylinder Nickel 30/30	5013969904086	83014011	6
SDN3040D	Easifit Cylinder Nickel 30/40	5013969904093	83014011	6
SDN3535D	Easifit Cylinder Nickel 35/35	5013969904109	83014011	6
SDN3545D	Easifit Cylinder Nickel 35/45	5013969904116	83014011	6
SDN4040D	Easifit Cylinder Nickel 40/40	5013969904123	83014011	6

SDN4050D	Easifit Cylinder Nickel 40/50	5013969904130	83014011	6
SDN4545D	Easifit Cylinder Nickel 45/45	5013969904147	83014011	6
SDN4555D	Easifit Cylinder Nickel 45/55	5013969904154	83014011	6

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	Kasp security products are guaranteed for 10 years against imperfect materials or workmanship Normal wear and tear or damage caused through attempted break-in is not covered
Country of origin	Taiwan

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
SDB3030D	60	17	32	189	110	20	185	218
SDB3040D	70	17	32	217	110	20	185	246
SDB3535D	70	17	32	217	110	20	185	246
SDB3545D	80	17	32	247	110	20	185	276
SDB4040D	80	17	32	247	110	20	185	276
SDB4050D	90	17	32	275	110	20	185	304
SDB4545D	90	17	32	305	110	20	185	334
SDB4555D	100	17	32	305	110	20	185	334
SDN3030D	60	17	32	189	110	20	185	218
SDN3040D	70	17	32	217	110	20	185	246
SDN3535D	70	17	32	217	110	20	185	246
SDN3545D	80	17	32	247	110	20	185	276
SDN4040D	80	17	32	247	110	20	185	276
SDN4050D	90	17	32	275	110	20	185	304
SDN4545D	90	17	32	305	110	20	185	334
SDN4555D	100	17	32	305	110	20	185	334

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
SDB3030D	200	115	120	1362		
SDB3040D	200	115	120	1530		
SDB3535D	200	115	120	1530		
SDB3545D	200	115	120	1710		
SDB4040D	200	115	120	1710		
SDB4050D	200	115	120	1878		
SDB4545D	200	115	120	2058		
SDB4555D	200	115	120	2058		
SDN3030D	200	115	120	1362		
SDN3040D	200	115	120	1530		
SDN3535D	200	115	120	1530		
SDN3545D	200	115	120	1710		
SDN4040D	200	115	120	1710		
SDN4050D	200	115	120	1878		
SDN4545D	200	115	120	2058		
SDN4555D	200	115	120	2058		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
SDB3030D	20	Blister	9	Card			54	Box
SDB3040D	20	Blister	9	Card			54	Box
SDB3535D	20	Blister	9	Card			54	Box
SDB3545D	20	Blister	9	Card			54	Box
SDB4040D	20	Blister	9	Card			54	Box
SDB4050D	20	Blister	9	Card			54	Box
SDB4545D	20	Blister	9	Card			54	Box
SDB4555D	20	Blister	9	Card			54	Box
SDN3030D	20	Blister	9	Card			54	Box
SDN3040D	20	Blister	9	Card			54	Box
SDN3535D	20	Blister	9	Card			54	Box
SDN3545D	20	Blister	9	Card			54	Box

SDN4040D	20	Blister	9	Card			54	Box
SDN4050D	20	Blister	9	Card			54	Box
SDN4545D	20	Blister	9	Card			54	Box
SDN4555D	20	Blister	9	Card			54	Box