


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [35150-0200](#)  
**Status:** **Active**  
**Overview:** [VersaBlade™](#)  
**Description:** 6.20mm Pitch Wire-to-Wire VersaBlade™ Hybrid Plug Housing, without Mounting Ears, 2 Circuits, Polyester UL94V-0, Natural

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-35150-002 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-35150-003 (PDF)</a>	



*image - Reference only*

**Agency Certification**

CSA	LR19980
TUV	R72090206
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">35150</a>
Application	Power, Wire-to-Wire
Comments	Polarized to Mating Part, Positive Lock
Overview	<a href="#">VersaBlade™</a>
Product Name	VersaBlade™

**Physical**


Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-30°C to +105°C

**Material Info**

UPC	800754375375
-----	--------------

**Reference - Drawing Numbers**

Packaging Specification	PK-35150-002
Product Specification	PS-35150-003
Sales Drawing	SD-35150-020*

<b>EU RoHS</b> <b>ELV and RoHS</b> <b>Compliant</b> <b>REACH SVHC</b> <b>Contains SVHC: No</b> <b>Low-Halogen Status</b> <b>Not Reviewed</b>	<b>China RoHS</b> 
--	--

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
35150Series

**Mates With**  
35151021\* Receptacle Housing

**Use With**  
357450\*10 VersaBlade™ Crimp Terminals