

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43030-0004](#)
Status: **Active**
Overview: Micro-Fit 3.0™ Connectors
Description: Micro-Fit 3.0™ Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Specification PS-43045 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	43030
Application	Power
Crimp Quality Equipment	Yes
Overview	Micro-Fit 3.0™ Connectors
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0™

Physical


Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm²	N/A

Material Info

UPC 800754320092

Reference - Drawing Numbers

Product Specification PS-43045, RPS-43045-003, RPS-43045-004
 Sales Drawing SD-43030-****



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[43030Series](#)

Mates With

[43031](#)

Use With

[43025](#) Receptacle Housing, [43645](#) Receptacle Housing, [44133](#) Panel Mount Receptacle Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for insulation OD 0.63-1.10mm - 26-30 AWG	0639001600

Hand Crimp Tool	<u>0638190000</u>
T2 Terminator™	<u>0639104400</u>
for insulation OD	
1.12-1.27mm - 26-30	
AWG	
Insertion Tool for	<u>0638120800</u>
Crimp Terminal	
FineAdjust™	<u>0639004400</u>
Applicator for	
insulation OD	
1.12-1.27mm - 26-30	
AWG	
Extraction Tool	<u>0011030043</u>
Japan	
Description	Product #
Applicator for M21 1A	<u>0572983000</u>
Bench Press, 20-30	
AWG Wire	

This document was generated on 06/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION