

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19154-0044](#)
Status: **Active**
Overview: [Splice](#)
Description: Step Down Butt Splice for 8-12 AWG Wire Red w/Yellow Strip

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19154](#)
 Comments Step down: 8 to 10/12 AWG . Red with Yellow Stripe
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Splice](#)
 Product Name Butt - Step Down

Physical

Barrel Type Closed - Brazed
 Color - Resin Red
 Flammability 94V-0
 Insulation PVC
 Material - Resin PVC
 Packaging Type Bag
 Temperature Range - Operating -40°C to +105°C
 Wire Insulation Diameter 9.65mm max.
 Wire Size AWG 10, 12, 8

Electrical


Voltage - Maximum 600V

Material Info

Old Part Number DC-654X

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
 Sales Drawing SD-19154-007



EU RoHS

**ELV and RoHS
 Compliant**
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[19154Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Putt Pump Dieless Head System	0192860065
Hand Crimp Tool	0640013900
Manual Putt Pump Hydraulic System, Die set required	0192860117
Die Set (large) for the HHLS Hydraulic Crimper	0192890001