

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19213-0009](#)  
**Status:** **Active**  
**Overview:** [Wire Pins](#)  
**Description:** Avikrimp™ Wire Pin Terminal for 22-18 AWG Wire, Loose in bag

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Crimp Terminals  
 Series [19213](#)  
 Application Power  
 Comments Pin Length 9.91mm  
 Crimp Quality Equipment Yes  
 MolexKits Yes  
 Overview [Wire Pins](#)  
 Product Name Wire Pin

**Physical**


Flammability 94V-2  
 Gender Male  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Packaging Type Bag  
 Plating min - Mating 1.016µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 6.35mm max.  
 Wire Size AWG 18, 19, 20, 22  
 Wire Size mm² N/A

**Material Info**

Old Part Number WP-8218

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19213-002



**EU RoHS**

**ELV and RoHS  
 Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
**Not Reviewed**

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

19213Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640050100</a>
Hand Crimp Tool	<a href="#">0640010100</a>