

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [03-09-1030](#)
Status: **Active**
Overview: Standard .093"
Description: 2.36mm Diameter Standard Receptacle Housing, 3 Circuit

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [6496](#)
 Application Power, Wire-to-Wire
 Comments Glow Wire Equivalent Part Number [50361875](#). 17.0A max. can be achieved when housing is used with 42477 or 42478 terminals
 Overview [Standard .093"](#)
 Product Name Standard .093"

Physical

Circuits (maximum) 3
 Circuits Detail 3
 Color - Resin Natural
 Flammability 94V-2
 Gender Female
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Nylon
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 5.03mm
 Stackable No
 Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 14A

Material Info

Old Part Number 6496-03RB
 UPC 800754942379

Reference - Drawing Numbers

Sales Drawing SD-6496-3R*




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

6496Series

Mates With

1396 Standard .093 Pin and Socket Plug Housing