

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [62201-8601](#)
Status: **Active**
Description: Press-In Tool Vertical Header 11-Row, 5-Column

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)


General

Product Family	Application Tooling
Series	T3002
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool

Material Info

Reference - Drawing Numbers

Application Tooling Documents ATS-622018601, TM-622018699, TM-622022099



EU RoHS	China RoHS
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[T3002Series](#)

Use With
 I-Trac™ Backplane Signal Module, [75705 Series](#)

Application Tooling Description	FAQ Product #
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 5 Columns, 110 Circuits, Mating Pin Length 4.70mm	0757050503
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 5 Columns, 110 Circuits, Mating Pin Length 5.70mm	0757050504

1.85mm by 3.70mm 0757051503
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Open Ends, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm

1.85mm by 3.70mm 0757051513
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Left End Wall, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm

1.85mm by 3.70mm 0757051525
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Dual End Walls, 11
Rows, 10 Columns,
220 Circuits,
Staggered Mating
Pin Length 4.70mm
& 5.70mm

1.85mm by 3.70mm 0757052503
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm

1.85mm by 3.70mm 0757053504
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 5.70mm

1.85mm by 3.70mm 0757059503
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Endwall, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm

1.85mm by 3.70mm 0757051504
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Open Ends, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 5.70mm

1.85mm by 3.70mm 0757051505
Pitch, GbX I-
Trac™ Vertical
Header Module,
Unguided, Open
Ends, 11 Rows,
5 Columns, 110

Circuits, Staggered
Mating Pin Length
4.70mm & 5.70mm,
Lead-Free
1.85mm by 3.70mm 0757051523
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Dual End Wall, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757051533
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Right End Wall, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757052504
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757053503
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757053505
Pitch, GbX I-
Trac™ Vertical
Header Module,
Left Guide, Right
Open, 11 Rows,
5 Columns, 110
Circuits, Staggered
Mating Pin Length
4.70mm & 5.70mm,
Lead-Free
1.85mm by 3.70mm 0757054503
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
5 Columns, 110
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757054504
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
5 Columns, 110
Circuits, Mating Pin
Length 5.70mm
1.85mm by 3.70mm 0757055503
Pitch, GbX I-Trac™

Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
5 Columns, 110
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757055504
Pitch, GbX I-Trac™

Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
5 Columns, 110
Circuits, Mating Pin
Length 5.70mm
1.85mm by 3.70mm 0757057503
Pitch, GbX I-Trac™

Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 5 Columns,
110 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757057505
Pitch, GbX I-Trac™

Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 5 Columns,
110 Circuits,
Staggered Mating
Pin Length 4.70mm
& 5.70mm, Lead-
Free
1.85mm by 3.70mm 0757059505
Pitch, GbX I-
Trac™ Vertical
Header Module,
Right Guide, Left
Endwall, 11 Rows,
5 Columns, 110
Circuits, Staggered
Mating Pin Length
4.70mm & 5.70mm,
Lead-Free

This document was generated on 04/02/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION