

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [62201-8603](#)
Status: **Active**
Description: Press-In Tool for Vertical Header 11-Row, 10-Column

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	T3002
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool

Material Info

Reference - Drawing Numbers

Application Tooling Documents ATS-622018603, TM-622018699, TM-622022099




image - Reference only

EU RoHS **China RoHS**

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[T3002Series](#)

Use With

GbX I-Trac™ Backplane Signal Module,
[75705 Series](#)

Application Tooling	FAQ
Description	Product #

1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating Pin Length 4.70mm	0757050103
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating Pin Length 5.70mm	0757050104

1.85mm by 3.70mm 0757050115
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Left End Wall, 11
Rows, 10 Columns,
220 Circuits,
Staggered Mating
Pin Length 4.70mm
& 5.70mm

1.85mm by 3.70mm 0757051123
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Dual End Wall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm

1.85mm by 3.70mm 0757053104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm

1.85mm by 3.70mm 0757053124
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm,
Orientation Key B

1.85mm by 3.70mm 0757054104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 5.70mm

1.85mm by 3.70mm 0757055104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 5.70mm

1.85mm by 3.70mm 0757056104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm

1.85mm by 3.70mm 0757057104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 10 Columns,

200 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757051103
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Open Ends, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757051104
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Open Ends, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757051113
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Left End Wall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757051124
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Dual End Walls, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757051133
Pitch, GbX I-Trac™
Vertical Header
Module, Unguided,
Right End Wall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757052103
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
200 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757052104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757053103
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,

200 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757053114
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm,
Orientation Key A
1.85mm by 3.70mm 0757054103
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757055103
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757057103
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 10 Columns,
200 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757059103
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Endwall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757059104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Endwall, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm

This document was generated on 04/02/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION