

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [502351-0600](#)
Status: **Active**
Overview: [DuraClik™](#)
Description: 2.00mm Pitch DuraClik™ Wire-to-Board Receptacle Housing, Single Row, 6 Circuits

Documents:

3D Model	Product Specification PS-502351-002 (PDF)
Drawing (PDF)	Packaging Specification PK-502351-001 (PDF)
Product Specification PS-502351-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	502351
Application	Signal, Wire-to-Board
Overview	DuraClik™
Product Name	DuraClik™

Physical

Circuits (maximum)	6
Color - Resin	White
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	3A
-------------------------------	----

Material Info

UPC	800756666860
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-502351-001
Product Specification	PS-502351-001, PS-502351-002, RPS-502351-001, RPS-502351-003, RPS-502351-004, RPS-502351-005
Sales Drawing	SD-502351-001




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[502351Series](#)

Mates With

[502352 PCB Header](#)

Use With

[50212 Crimp Terminal](#) . [50372 Crimp Terminal](#)