
Item no.: 281-637
Product description: 3-CONDUCTOR GROUND TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Weight	15.609 g
Color	green-yellow
Wiring type	Angled Type
No. of connection Points	3
No. of potentials	1
Height	37 mm
Height	1.46 in
Width	6 mm
Width	0.236 in
Depth	61.5 mm
Depth	2.42 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0.37 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-637	ABS	05-HG476175/3-PDA			2,5
281-637	BV	07436/C0			2,5
281-637	CCA	NL5591/1			4
281-637	CSA	154112-1505034			28-12
281-637	GL	17295-00HH			4
281-637	KEMA	2076376.01			4
281-637	KR	HMB05880-EL001	500/800	10/35	4
281-637	PRS	TE/1718/880590/08			4
281-637	UR	E45172			28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected