

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **08-56-0108**  
**Status:** **Active**  
**Overview:** KK® Interconnection System  
**Description:** 3.96mm Pitch KK® Crimp Terminal 2578, 22-26 AWG, Bag, Brass, 0.51µm Selective Gold (Au)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-08-50 \(PDF\)](#)

**General**

|                         |                                   |
|-------------------------|-----------------------------------|
| Product Family          | Crimp Terminals                   |
| Series                  | <u>2578</u>                       |
| Application             | Power                             |
| Crimp Quality Equipment | Yes                               |
| Overview                | <u>KK® Interconnection System</u> |
| Product Name            | KK®                               |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Gender                         | Female               |
| Material - Metal               | Brass                |
| Material - Plating Mating      | Gold                 |
| Material - Plating Termination | Gold                 |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 0.381µm              |
| Plating min - Termination      | 0.051µm              |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.65mm max.          |
| Wire Size AWG                  | 22, 24, 26           |
| Wire Size mm²                  | N/A                  |

**Material Info**

|                 |             |
|-----------------|-------------|
| Old Part Number | 2578-(550)L |
|-----------------|-------------|

**Reference - Drawing Numbers**

|                       |          |
|-----------------------|----------|
| Product Specification | PS-08-50 |
| Sales Drawing         | SD-2578  |



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[2578Series](#)

**Use With**

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) , [5239](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                         | Product #                  |
|-------------------------------------|----------------------------|
| Hand Crimp Tool for Crimp Terminals | <a href="#">0638117400</a> |
| Extraction Tool                     | <a href="#">0011030016</a> |