


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [503149-2800](#)
Status: **Active**
Overview: [CLIK-Mate™ Wire-to-Board Connectors](#)
Description: 1.50mm Pitch CLIK-Mate™ Wire-to-Board Housing, Dual Row, Positive Lock, 28 Circuits

Documents:

3D Model	Application Specification AS-503149-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-503149-001 (PDF)
Product Specification PS-503148-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-503154-001 (PDF)	



General

Product Family	Crimp Housings
Series	503149
Application	Signal, Wire-to-Board
Overview	CLIK-Mate™ Wire-to-Board Connectors
Product Name	CLIK-Mate™

Physical

Circuits (maximum)	28
Color - Resin	Beige
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25°C to +85°C

Electrical

Current - Maximum per Contact	2A
-------------------------------	----

Material Info

UPC	883906271633
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-503149-001
Packaging Specification	SPK-503149-001
Product Specification	PS-503148-001, PS-503154-001, RPS-503148-001, RPS-503148-003, RPS-503154-001, RPS-503154-002, RPS-503154-003, RPS-503154-004, RPS-503154-005, RPS-503154-007, RPS-503154-008, RPS-503154-009, RPS-503354-001
Sales Drawing	SD-503149-001

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

503149Series

Mates With

503154 PCB Receptacle

Use With

502579 Crimp Terminal