

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [180081-4250](#)
Status: **Active**
Overview: [Down Light Modules](#)
Description: Down Light Module 80mm, Wide Flood - 50°, Neutral (4100K), Standard Flux

Documents:

3D Model	Product Literature (PDF)
Drawing (PDF)	Installation Guide (PDF)
RoHS Certificate of Compliance (PDF)	

Agency Certification

UL E328924

General

Product Family	Solid State Lighting
Series	180081
Beam Angle	24°, 32°, and 50°
Comments	Commercially Configurable to 700mA, 1050mA, and 1400mA
Installation Guide Order No	987650-4385
Overview	Down Light Modules
Product Literature Order No	987650-4381
Product Name	Down Light Module
Type	LED Puck Module

Physical

Base Type	Socket
Color Rendering Index (CRI)	80
Correlated Color Temp (CCT)	4100K
Lamp Type	Light Module
Packaging Type	Individual Carton

Electrical

Lamp Wattage - Maximum	12.4W, 17.2W, 7.9W
Lumens	1020, 550, 800
Voltage (Fixture) - Maximum	11.4V, 11.9V, 12.3V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-180081-000



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[180081Series](#)