

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [180081-4350](#)  
**Status:** **Active**  
**Overview:** [Down Light Modules](#)  
**Description:** Down Light Module 80mm, Wide Flood - 50°, Neutral (4100K), High Flux

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Installation Guide (PDF)</a>
<a href="#">RoHS Certificate of Compliance (PDF)</a>	

**Agency Certification**

UL E328924

**General**

Product Family	Solid State Lighting
Series	<a href="#">180081</a>
Beam Angle	24°, 32°, and 50°
Comments	Commercially Configurable to 700mA, 1050mA, and 1400mA
Installation Guide Order No	987650-4385
Overview	<a href="#">Down Light Modules</a>
Product Literature Order No	987650-4381
Product Name	Down Light Module
Type	LED Puck Module

**Physical**

Base Type	Socket
Color Rendering Index (CRI)	80
Correlated Color Temp (CCT)	4100K
Lamp Type	Light Module
Packaging Type	Individual Carton

**Electrical**

Lamp Wattage - Maximum	12W, 18.8W, 25.8W
Lumens	1200, 1530, 840
Voltage (Fixture) - Maximum	17.2V, 17.9V, 18.5V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing SD-180081-000



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[180081Series](#)